



85241129

### Shutter push-button, Q.x, p. white velvety

#### Technical characteristics

#### Functions

Venetian blind movement time 2 mn

#### Main electrical features

Nominal voltage 12 V

Frequency - Hz

#### Detection

Sensor Not suitable for rain and wind sensors

#### Materials

Colour of design line polar white

Colour polarwhite

Material thermoplastic

#### Installation, mounting

Installation mode clamp fastening

#### Settings

Lamella adjusting time (adjustable) 50 ms...2.5 s

Minimum slat adjustment time ≈ 250 ms

Delay time, adjustable 0...500 s

Lamella adjustment on button-press < 0.4 s

#### Equipment

Self-retaining for 2 min on button-press > 0.4 s

Change-over time for change of direction < 0.6 s

#### Safety

Protection with dismantling protection

#### Use conditions

Operating temperature -5...45 °C

Relative humidity (without condensation) 0...65 % (without condensation)

#### Identification

Application, usage Blind control

Main design line Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s) Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

#### Instructions

