



85241173

**Shutter push-button, K.5, stainless steel matt, lacq.**

**Technical characteristics**

**Functions**

Venetian blind movement time 2 mn

Function Memory function for automatic execution of learned up and down times with position ; Party function, no execution of automatic, radio and extension unit commands (lock-out protection)

**Controls and indicators**

Operation activation of the party function using buttons in up and down direction > 20 sec.

**Main electrical features**

Nominal voltage 12 V

Frequency - Hz

**Detection**

Sensor Not suitable for rain and wind sensors

**Materials**

Colour of design line stainless steel

Material / workmanship lacquered

**LED control**

LED LED application module/insert compatibility display ; with status LED for memory and party function, red/orange ; with indicator LED for lock-out protection

**Installation, mounting**

Installation mode clamp fastening

**Settings**

Lamella adjusting time (adjustable) 50 ms...2.5 s

Minimum slat adjustment time ≈ 250 ms

Delay time, adjustable 0...500 s

Lamella adjustment on button-press < 0.4 s

**Equipment**

Self-retaining for 2 min on button-press > 0.4 s

Change-over time for change of direction < 0.6 s

**Safety**

Halogen free No

Protection with dismantling protection

**Use conditions**

---

Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)

---

**Identification**

---

Application, usage	Blind control
Main design line	Berker K.5
Secondary design line(s)	Electronics platform ; Berker K.5

---

**Instructions**

---

Special note text	Can be switched to orientation led by extension unit.
-------------------	---

---