



80162869

IP20



Push-button 2gang, + RGB LED, internal temp. sensor, KNX - R.1/R.3, p.white gl.

Technical characteristics

Functions

With room temperature controller	No
----------------------------------	----

operating concept "independent push-button" function predefined ; operating concept for "roller shutter/blind" function predefined ; switching of scenes (1..8) possible ; Orientation LED can be controlled via object ; brightness value of the status LED for day/nighttime operation preset, status LED for day/nighttime operation can be controlled via object ; integrated temperature sensor with output of the measured values ; Colour of status LED uniformly adjustable for complete device ; push-button functions: including switching, dimming, roller shutter/blind, timer, priority, temperature setpoint adjustment, operating mode changeover

Easy link functions

Function	Function for manual interruption of automatic functions already triggered
----------	---------------------------------------------------------------------------

Function

operating surfaces as buttons (single-surface operation) and rockers (two-surface operation) ; the brightness of status LEDs are individually adjustable for button/ rocker function ; brightness value of the status LEDs for day/nighttime operation adjustable via object or manually ; value transmitter for dimming, position, brightness temperature values 1 and 2 byte ; button/rocker functions for switching, dimming, roller shutter/blind, value transmitter 1/2 byte, room thermostat extension unit, priority, scene, automatic control deactivation ; integrated temperature sensor with output of the measured values via object ; button functions for switching, dimming, roller shutter/blind, timer, value transmitter 1/2 byte, room thermostat extension unit, priority, scene, 2-channel mode, step switch, automatic control deactivation ; rocker functions for switching, dimming, roller shutter/blind, value transmitter 1/2 byte, room thermostat extension unit, priority, scene, 2-channel mode, automatic control deactivation ; parameter defineable lock function ; 3-step switch, function for incremental selection of up to 7 stored values ; Status LED configurable in its colour per button

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--------------------------------------------

Controls and indicators

With LED indication	Yes
---------------------	-----

Number of buttons	2
-------------------	---

Operation

operating areas configurable as one or two-area operation

Electric current

Bus current consumption (data transfer)	max. 20 mA
-----------------------------------------	------------

Power

Power consumption, KNX

≈ 150 mW

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	-----------------------------------------------------------------------------------------

Screen

With display	No
--------------	----

Materials

Colour independent of design lines	polar white
------------------------------------	-------------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Surface appearance	glossy
--------------------	--------

Surface protection	Brilliant
--------------------	-----------

Type of surface treatment	untreated
---------------------------	-----------

Material family	Plastic
-----------------	---------

LED control

LED	with white operating LED ; with 2 RGB status LEDs per rocker
-----	--------------------------------------------------------------

Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

Settings

Supported configuration modes	system, easy
-------------------------------	--------------

Parameterisation	single and two push-button operation parameterisable
------------------	------------------------------------------------------

Scope of delivery

Bus connection included	No
-------------------------	----

Equipment

Number of actuation points	4
----------------------------	---

With anti-theft/dismantling protection	No
----------------------------------------	----

Product type:	product type: push-button 2gang
---------------	---------------------------------

Use

Differentiation characteristic 2 - Sales	and RGB LED
------------------------------------------	-------------

Differentiation characteristic 3 - Sales	with integrated temperature sensor
------------------------------------------	------------------------------------

Safety

Halogen free	No
--------------	----

Protection	with dismantling protection
------------	-----------------------------

Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte
-------	---------------------------------------------------------------------------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Storage/transport temperature	-20...70 °C (storage at > 45°C reduces the service life)
-------------------------------	----------------------------------------------------------

Temperature	integrated temperature sensor with output of the measured values via object
-------------	-----------------------------------------------------------------------------

Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker R.1/R.3/Serie 1930/R.classic
Secondary design line(s)	KNX ; Berker R.3 ; Serie 1930 ; Series R.classic
Instructions	
Special note text	Use only in conjunction with bus coupling unit 8004 00 01!