



85341179

**Motion det. 1.1 m, K.1, p. white glossy**

**Technical characteristics**

**Functions**

Mode of operation	μ-processor controlled mode of operation
Function	Teach function for response brightness via button ; with keylock ; Party function for switching on for 2 hours ; with memory function for presence simulation

**Controls and indicators**

Button / push-button	with button for on/off/automatic
----------------------	----------------------------------

**Dimensions**

Assembling height	34 mm
Nominal mounting height	1.1 m

**Measurement**

Detection field, rectangular shaped	≈ 12 x 16 m
-------------------------------------	-------------

**Reach distance**

Range, frontal	≈ 12 m
Range, side	each ≈ 8 m

**Detection**

Number of detection levels	3
Detection angle, settable	each side ≈ 45...90 °
Detection field Ø, on floor	0 m

**Materials**

Colour of design line	polar white
-----------------------	-------------

**Lighting control**

Response brightness, adjustable	≈ 5...1000 lx , daytime operation
---------------------------------	-----------------------------------

**LED control**

LED	with operation and status LED, red/green/orange ; LED application module/insert compatibility display
-----	---

**Settings**

Response value luminosity adjustable	Yes
Response value sensitivity adjustable	Yes
Response sensitivity, settable	10...100 %
Delay time	≈ 180 s
Switch-off pre-warning to dimming value 50% for	30 s

**Safety**

REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection

**Use conditions**

Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)

**Identification**

Application, usage	Light control ; Motion detector
Main design line	Berker K.1
Secondary design line(s)	Motion detector ; Berker K.1

**Instructions**

Information text	Continuous direct sunlight penetrating the upward-pointing detection plane can result in failure of the motion detector. Only suitable for indoor areas!
------------------	--