



85341229

IR motion det. comf 1.1 m, Q.x, p. white velvety

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

Function	with keylock
----------	--------------

Controls and indicators

Button / push-button	with button for on/off/automatic
----------------------	----------------------------------

Main electrical features

Nominal voltage	230 V AC
Frequency	50/60 Hz

Dimensions

Assembling height	34 mm
Nominal mounting height	1.1 m

Tripping

immunity time	≈ 10 s
---------------	--------

Measurement

Detection field, rectangular shaped	≈ 12 x 16 m
-------------------------------------	-------------

Reach distance

Range, frontal	≈ 12 m
----------------	--------

Detection

Number of detection levels	3
Detection angle	180 °
Detection angle, settable	each side ≈ 45...90 °
Detection field Ø, on floor	0 m

Materials

Colour of design line	polar white
Colour	polarwhite
Material	thermoplastic

Lighting control

Response brightness, adjustable	≈ 5...1000 lx , daytime operation
---------------------------------	-----------------------------------

Settings

Response value luminosity adjustable	Yes
--------------------------------------	-----

Response value sensitivity adjustable	Yes
Response sensitivity, settable	10...100 %
Short time mode	200 ms
Delay time	≈ 180 s
Delay time, adjustable	≈ 10 s...30 mn
Switch-off pre-warning to dimming value 50% for	30 s
Safety	
Protection index IP	IP20
REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection
Use conditions	
Operating temperature	-5...45 °C
Relative humidity (without condensation)	0...65 % (without condensation)
Identification	
Application, usage	Light control, Motion detector
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9
Instructions	
Information text	Continuous direct sunlight penetrating the upward-pointing detection plane can result in failure of the motion detector. Only suitable for indoor areas!