




80960229

IP20



## Cover for 1gang for push-button module, clearlens, Q.x, p. white velvety

### Technical characteristics

#### Architecture

Fixing mode flush-mounting

#### Functions

operating concept "independent push-button" function predefined ; operating concept for "roller shutter/blind" function predefined ; switching of scenes (1..8) possible ; brightness value of the status LED for day/nighttime operation preset, change-over for day/nighttime operation possible ; integrated temperature sensor with output of the measured values ; Colour of status LED uniformly adjustable for complete device ; push-button functions: including switching, dimming, roller shutter/blind, timer, priority, operating mode changeover

Easy link functions

Function Function for manual interruption of automatic functions already triggered

operating surfaces as buttons (single-surface operation) and rockers (two-surface operation) ; the brightness of status LEDs are individually adjustable for button/ rocker function ; brightness value of the status LEDs for day/nighttime operation adjustable via object or manually ; value transmitter for dimming, position, brightness temperature values 1 and 2 byte ; integrated temperature sensor with output of the measured values via object ; parameter defineable lock function ; button/rocker functions for switching, dimming, roller shutter/blind, value transmitter 1/2 byte, room thermostat extension unit, priority, scene, automatic control deactivation

Function

#### Controls and indicators

Operation operating areas configurable as one or two-area operation

Button / push-button with programming button and red programming LED

#### Voltage

Operating voltage over bus 21...32 V DC

#### Dimensions

Height 58 mm

#### Power

Power consumption, KNX ≈ 108 mW

#### Camera

Lens with clear lens for RGB status display of the push-button module

#### Materials

Colour of design line	polar white
RAL colour	RAL 9010 - Pure white
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	velvety
Type of surface treatment	Painted
<b>Connection</b>	
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal
<b>Settings</b>	
Supported configuration modes	system, easy
<b>Equipment</b>	
Buzzer/siren	with integrated buzzer for acoustic identification of the device within the system
<b>Use</b>	
Differentiation characteristic 2 - Sales	with clear lens
<b>Safety</b>	
Protection index IP	IP20
Protection	with dismantling protection
<b>Use conditions</b>	
Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C (storage at > 45°C reduces the service life)
Temperature	integrated temperature sensor with output of the measured values via object
<b>Identification</b>	
Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker Q.1/Q.3
Secondary design line(s)	KNX ; Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9