




80960282

IP20



Cover for 1gang for push-button module, clearlens, S.1/B.3/B.7, white glossy

Technical characteristics

Architecture

Fixing mode flush-mounting

Functions

operating concept "independent push-button" function predefined ; operating concept for "roller shutter/blind" function predefined ; switching of scenes (1..8) possible ; brightness value of the status LED for day/nighttime operation preset, change-over for day/nighttime operation possible ; integrated temperature sensor with output of the measured values ; Colour of status LED uniformly adjustable for complete device ; push-button functions: including switching, dimming, roller shutter/blind, timer, priority, operating mode changeover

Easy link functions

Controls and indicators

Button / push-button with programming button and red programming LED

Voltage

Operating voltage over bus 21...32 V DC

Dimensions

Height 55 mm

Power

Power consumption, KNX \approx 108 mW

Materials

Colour of design line white

RAL colour RAL 1013 - Oyster white

Material thermoplastic

Type of surface treatment untreated

Connection

Bus coupling unit with integral bus coupling unit

Bus connection bus connection via connecting terminal

Settings

Supported configuration modes system

Use

Differentiation characteristic 2 - Sales with clear lens

Safety

Protection index IP	IP20
Protection	with dismantling protection
Use conditions	
Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C (storage at > 45°C reduces the service life)
Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker S.1/B.3/B.7
Secondary design line(s)	KNX, Berker S.1, Berker B.3, Berker B.7