



80960373

IP20



Cover f. 2gang f. push-button module, clearlens, K.5, stainl. steel matt, lacq.

Technical characteristics

Architecture

Fixing mode flush-mounting

Functions

operating concept "independent push-button" function predefined ; operating concept for "roller shutter/blind" function predefined ; switching of scenes (1..8) possible ; brightness value of the status LED for day/nighttime operation preset, change-over for day/nighttime operation possible ; integrated temperature sensor with output of the measured values ; Colour of status LED uniformly adjustable for complete device ; push-button functions: including switching, dimming, roller shutter/blind, timer, priority, operating mode changeover

Easy link functions

Controls and indicators

Button / push-button with programming button and red programming LED

Voltage

Operating voltage over bus 21...32 V DC

Dimensions

Height 55 mm

Power

Power consumption, KNX \approx 108 mW

Camera

Lens with 2 clear lenses for the RGB status display of the push-button module

Materials

Colour of design line stainless steel

RAL colour RAL 9022 - Pearl light grey

Material thermoplastic

Surface appearance matt

Type of surface treatment Painted

Connection

Bus coupling unit with integral bus coupling unit

Bus connection bus connection via connecting terminal

Settings

Supported configuration modes system

Use

Differentiation characteristic 2 - Sales

with clear lens

Safety

Protection index IP

IP20

Protection

with dismantling protection

Use conditions

Operating temperature

-5...45 °C

Storage/transport temperature

-20...70 °C (storage at > 45°C reduces the service life)

Identification

Application, usage

KNX - operating systems

Product family

product family: push-button

Main design line

KNX - Berker K.1/K.5

Secondary design line(s)

KNX, Berker K.1, Berker K.5