



80960385

IP20



## Cover for 2gang for push-button module, clearlenses, S.1/B.3/B.7, ant., matt

### Technical characteristics

#### Functions

operating concept "independent push-button" function predefined ; operating concept for "roller shutter/blind" function predefined ; switching of scenes (1..8) possible ; brightness value of the status LED for day/nighttime operation preset, change-over for day/nighttime operation possible ; integrated temperature sensor with output of the measured values ; Colour of status LED uniformly adjustable for complete device ; push-button functions: including switching, dimming, roller shutter/blind, timer, priority, operating mode changeover

#### Easy link functions

Function Function for manual interruption of automatic functions already triggered

operating surfaces as buttons (single-surface operation) and rockers (two-surface operation) ; the brightness of status LEDs are individually adjustable for button/ rocker function ; brightness value of the status LEDs for day/nighttime operation adjustable via object or manually ; value transmitter for dimming, position, brightness temperature values 1 and 2 byte ; integrated temperature sensor with output of the measured values via object ; parameter defineable lock function ; button/rocker functions for switching, dimming, roller shutter/blind, value transmitter 1/2 byte, room thermostat extension unit, priority, scene, automatic control deactivation

### Controls and indicators

Operation operating areas configurable as one or two-area operation

Button / push-button with programming button and red programming LED

### Voltage

Operating voltage over bus 21...32 V DC

### Dimensions

Height 55 mm

### Power

Power consumption, KNX ≈ 108 mW

### Camera

Lens with 2 clear lenses for the RGB status display of the push-button module

### Materials

Colour of design line anthracite

Surface appearance matt

Type of surface treatment untreated

**Connection**

Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

**Settings**

Supported configuration modes	system, easy
-------------------------------	--------------

**Equipment**

Buzzer/siren	with integrated buzzer for acoustic identification of the device within the system
--------------	--

**Use**

Differentiation characteristic 2 - Sales	with clear lenses
--	-------------------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection

**Use conditions**

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C (storage at > 45°C reduces the service life)
Temperature	integrated temperature sensor with output of the measured values via object

**Identification**

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker S.1/B.3/B.7
Secondary design line(s)	KNX ; Berker S.1 ; Berker B.3 ; Berker B.7