




80960389

IP20



**Cover f. 2gang f. push-button module, clearlenses, S.1/B.3/B.7, p.white glossy**

**Technical characteristics**

**Architecture**

Fixing mode flush-mounting

**Functions**

operating concept "independent push-button" function predefined ; operating concept for "roller shutter/blind" function predefined ; switching of scenes (1..8) possible ; brightness value of the status LED for day/nighttime operation preset, change-over for day/nighttime operation possible ; integrated temperature sensor with output of the measured values ; Colour of status LED uniformly adjustable for complete device ; push-button functions: including switching, dimming, roller shutter/blind, timer, priority, operating mode changeover

Easy link functions

**Controls and indicators**

Button / push-button with programming button and red programming LED

**Voltage**

Operating voltage over bus 21...32 V DC

**Dimensions**

Height 55 mm

**Power**

Power consumption, KNX ≈ 108 mW

**Camera**

Lens with 2 clear lenses for the RGB status display of the push-button module

**Materials**

Colour of design line polar white

RAL colour RAL 9010 - Pure white

Material thermoplastic

Type of surface treatment Painted

**Connection**

Bus coupling unit with integral bus coupling unit

Bus connection bus connection via connecting terminal

**Settings**

Supported configuration modes system

**Safety**

Protection index IP	IP20
Protection	with dismantling protection
<b>Use conditions</b>	
Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C (storage at > 45°C reduces the service life)
<b>Identification</b>	
Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker S.1/B.3/B.7
Secondary design line(s)	KNX, Berker S.1, Berker B.3, Berker B.7