



85145131



IP20

quicklink

KNX radio button 1gang quicklink, R.1/R.3/1930/R.cl., black glossy

Technical characteristics

Functions

ETS additional functions	ETS additional functions: +6 scenes, 1 button control up/down, operating mode on/off, dimming value, brightness display, push-button, status display, forced control
--------------------------	--

Function	Configurable transmission and/or reception behaviour ; reset function (to factory setting) ; easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control
----------	--

Light scenes	scene saving lockable
--------------	-----------------------

Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory
---------------------	--

Controls and indicators

Operation	operating areas configurable as one or two-area operation
-----------	---

Button / push-button	with configuration and function button
----------------------	--

Connectivity

Radio protocol	KNX Radio
----------------	-----------

Receiver category	2
-------------------	---

Dimensions

Diameter	57.4 mm
----------	---------

Power

Radio transmission power	< 10 mW
--------------------------	---------

Materials

Colour of labelling	217,217,217
---------------------	-------------

Colour of design line	black
-----------------------	-------

Material for printing	PC-PMA black
-----------------------	--------------

Surface appearance	glossy
--------------------	--------

LED control

LED	with configuration and function LEDs ; LED application module/insert compatibility display
-----	--

Connection

Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
----------------	--

Settings

top and bottom operating area on 1-gang switching/dimming inserts and network insert are freely configurable ; toolless quicklink configuration using buttons and LED display

Programming

Equipment

Number of radio channels	2
Number of quicklink links	max. 20 transmitter/receiver
Type of configuration	Laserdruck
Transmitter duty cycle	1 %

Brightness switch-on brightness level for each operating area on configuration with dimmer insert, power failure proof, storable

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)

Identification

Application, usage	Light control ; KNX radio- operating systems
Main design line	Berker R.1/R.3/R.8/Serie 1930/R.classic
Secondary design line(s)	Electronics platform ; Berker R.1 ; Berker R.3 ; Serie 1930 ; Series R.classic

Instructions

Special note text Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!