


85145131



IP20

## KNX radio button 1gang quicklink, R.1/R.3/1930/R.cl., black glossy

### Technical characteristics

#### Functions

ETS additional functions	ETS additional functions: +6 scenes, 1 button control up/down, operating mode on/off, dimming value, brightness display, push-button, status display, forced control
Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

#### Connectivity

Radio protocol	KNX Radio
Receiver category	2

#### Dimensions

Diameter	57.4 mm
----------	---------

#### Power

Radio transmission power	< 10 mW
--------------------------	---------

#### Materials

Colour of labelling	217,217,217
Colour of design line	black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Material for printing	PC-PMA black

#### Equipment

Number of radio channels	2
Number of quicklink links	max. 20 transmitter/receiver
Type of configuration	Laserdruck
Transmitter duty cycle	1 %

#### Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection

#### Use conditions

Operating temperature	-5...45 °C
Relative humidity (without condensation)	0...65 % (without condensation)

#### Identification

Application, usage	Light control, KNX radio- operating systems
Main design line	Berker R.1/R.3/R.8/Serie 1930/R.classic
Secondary design line(s)	Berker R.1, Berker R.3, Serie 1930, Series R.classic

---

**Instructions**

Special note text	Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!
-------------------	--