



85421100

Universal Push button Dimmer 1gang (R,L, C, LED)

Technical characteristics

Functions

Soft startup bulb-preserving soft startup

Main electrical features

Frequency 50/60 Hz

Voltage

Operating voltage 230 V AC

Fuse

Fuse short-circuit and overload proof (electronic fuse)

Dimensions

Insertion depth 32 mm

Power

Dimmable electronic transformers and bi-mode transformers 20...400 VA

Dimmable conventional transformers 20...200 VA

Power consumption (standby) < 0.3 W

Materials

Colour not applicable

Material Plastic/metal

LED control

Dimmable 230 V retrofit LED lamps 3...120 W

Incandescent bulbs control

230 V incandescent lamps and halogen lamps 20...350 W

Installation, mounting

Installation mode with spreader claws

Connection

Type of connection with screw terminals

Cable

Load cable length max. 100 m

Use conditions

Operating temperature -5...45 °C

Identification

Application, usage Motion detector, KNX radio- operating systems, Light control

Instructions

Special note text Caution! Only connect dimmable 230 V ESL or retrofit-LED lamps.

Information text Do not use non-dimmable energy-saving lamps and 230 V LED lamps.