



85421201

## Universal touch dimmer 1gang, 1930/R.classic

### Technical characteristics

#### Functions

Soft startup	bulb-preserving soft startup
--------------	------------------------------

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Voltage

Operating voltage	230 V AC
-------------------	----------

#### Fuse

Fuse	short-circuit and overload proof (electronic fuse)
------	--

#### Dimensions

Insertion depth	32 mm
-----------------	-------

#### Power

Dimmable conventional transformers	25...400 VA
Power consumption (standby)	< 0.3 W
Electronic transformers and dual-mode transformers	25...400 W

#### Materials

Colour	not applicable
Material	Plastic/metal

#### Fluorescent bulbs control

Dimmable energy-saving lamps	13...80 W
------------------------------	-----------

#### LED control

Dimmable 230 V retrofit LED lamps	5...70 W
-----------------------------------	----------

#### Incandescent bulbs control

230 V incandescent lamps and halogen lamps	25...400 W
--	------------

#### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

#### Connection

Type of connection	with screw terminals
Number of substations	unlimited

#### Cable

Load cable length	max. 100 m
Cable length, extensions	max. 50 m
<b>Equipment</b>	
Substation input	Yes
Dimming principle	phase cut-on or cut-off according to load type, self-learning
<b>Safety</b>	
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
<b>Use conditions</b>	
Operating temperature	-5...45 °C
Relative humidity (without condensation)	0...65 % (without condensation)
<b>Identification</b>	
Application, usage	Light control, KNX radio- operating systems, Motion detector
Secondary design line(s)	Serie 1930, Series R.classic