



85648126



IP20

quicklink

KNX radio button 4gang quicklink, Q.x, ant. velvety, lacq.

Technical characteristics

Functions

ETS additional functions	ETS additional functions: +6 scenes, 1 button control up/down, operating mode on/off, dimming value, brightness display, push-button, status display, forced control
--------------------------	--

Function	Functions for the push-button operation areas up/down or left/right can be freely configured as receiver for controlling the connected load and as transmitter for remote control of a blind, for example ; reset function (to factory setting) ; Configurable transmission and/or reception behaviour
----------	--

Light scenes	scene saving lockable
--------------	-----------------------

Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory
---------------------	--

Controls and indicators

Operation	operating areas configurable as one or two-area operation
-----------	---

Button / push-button	with configuration and function button
----------------------	--

Connectivity

Radio protocol	KNX Radio
----------------	-----------

Receiver category	2
-------------------	---

Power

Radio transmission power	< 10 mW
--------------------------	---------

Materials

Colour of design line	anthracite
-----------------------	------------

Material / workmanship	lacquered
------------------------	-----------

Surface appearance	velvety
--------------------	---------

LED control

LED	with configuration and function LEDs ; LED application module/insert compatibility display
-----	--

Connection

Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
----------------	--

Settings

Programming	toolless quicklink configuration using buttons and LED display
-------------	--

Equipment

Number of radio channels	4
--------------------------	---

Number of quicklink links	max. 20 transmitter/receiver
Transmitter duty cycle	1 %
Brightness	switch-on brightness level for each operating area on configuration with dimmer insert, power failure proof, storable
Safety	
REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection
Use conditions	
Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)
Identification	
Application, usage	Light control ; KNX radio- operating systems
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
Instructions	
Information text	Extended operating options on 1gang inserts through 2 additional, freely-configurable radio channels.