


85648126



IP20

**KNX radio button 4gang quicklink, Q.x, ant. velvety, lacq.**

**Technical characteristics**

**Functions**

ETS additional functions	ETS additional functions: +6 scenes, 1 button control up/down, operating mode on/off, dimming value, brightness display, push-button, status display, forced control
Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

**Connectivity**

Radio protocol	KNX Radio
Receiver category	2

**Power**

Radio transmission power	< 10 mW
--------------------------	---------

**Materials**

Colour of design line	anthracite
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	velvety

**Equipment**

Number of radio channels	4
Number of quicklink links	max. 20 transmitter/receiver
Transmitter duty cycle	1 %

**Safety**

Protection	with dismantling protection
------------	-----------------------------

**Use conditions**

Operating temperature	-5...45 °C
Relative humidity (without condensation)	0...65 % (without condensation)

**Identification**

Application, usage	Light control, KNX radio- operating systems
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

**Instructions**

Information text	Extended operating options on 1gang inserts through 2 additional, freely-configurable radio channels.
------------------	---

