



85221101

Blind insert comf, 1930/R.classic

Technical characteristics

Functions

Power reserve	0 h
---------------	-----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Switching current (ohmic/inductive)	max. 5 A
-------------------------------------	----------

Switching current at $\cos \varphi = 0.6$	max. 3 A
---	----------

Dimensions

Insertion depth	32 mm
-----------------	-------

Claw guidance installation depth	32 mm
----------------------------------	-------

Housing installation depth	22 mm
----------------------------	-------

Materials

Material	Plastic/metal
----------	---------------

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Type of connection	with screw terminals
--------------------	----------------------

Number of substations	unlimited
-----------------------	-----------

Cable

Load cable length	max. 100 m
-------------------	------------

Cable length, extensions	max. 50 m
--------------------------	-----------

Equipment

Change-over time for change of direction	< 0.6 s
--	---------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Relative humidity (without condensation)	0...65 % (without condensation)
--	---------------------------------

Identification

Application, usage	Blind control, KNX radio- operating systems
--------------------	---

Main design line	Serie 1930/R.classic
------------------	----------------------

Secondary design line(s)	Serie 1930, Series R.classic
--------------------------	------------------------------