



85241124

Blind button Q.x alu velvety, lacquered

Technical characteristics

Functions

Venetian blind movement time	2 mn
------------------------------	------

Main electrical features

Nominal voltage	12 V
Frequency	- Hz

Detection

Sensor	Not suitable for rain and wind sensors
--------	--

Materials

Colour	aluminium
Material / workmanship	lacquered
Material	thermoplastic

Installation, mounting

Installation mode	clamp fastening
-------------------	-----------------

Settings

Lamella adjusting time	(adjustable) 50 ms...2.5 s
Minimum slat adjustment time	≈ 250 ms
Delay time, adjustable	0...500 s
Lamella adjustment on button-press	< 0.4 s

Equipment

Self-retaining for 2 min on button-press	> 0.4 s
Change-over time for change of direction	< 0.6 s

Safety

Protection	with dismantling protection
------------	-----------------------------

Use conditions

Operating temperature	-5...45 °C
Relative humidity (without condensation)	0...65 % (without condensation)

Identification

Application, usage	Blind control
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

Instructions

