



85241173

Shutter push-button, K.5, stainless steel matt, lacq.

Technical characteristics

Functions

Venetian blind movement time	2 mn
------------------------------	------

Function	Memory function for automatic execution of learned up and down times with position, Party function, no execution of automatic, radio and extension unit commands (lock-out protection)
----------	--

Controls and indicators

Operation	activation of the party function using buttons in up and down direction > 20 sec.
-----------	---

Main electrical features

Nominal voltage	12 V
Frequency	- Hz

Detection

Sensor	Not suitable for rain and wind sensors
--------	--

Materials

Colour of design line	stainless steel
Colour	stainless steel
Material / workmanship	lacquered
Material	thermoplastic

LED control

LED	LED application module/insert compatibility display, with status LED for memory and party function, red/orange, with indicator LED for lock-out protection
-----	--

Installation, mounting

Installation mode	clamp fastening
-------------------	-----------------

Settings

Lamella adjusting time	(adjustable) 50 ms...2.5 s
Minimum slat adjustment time	≈ 250 ms
Delay time, adjustable	0...500 s
Lamella adjustment on button-press	< 0.4 s

Equipment

Self-retaining for 2 min on button-press	> 0.4 s
Change-over time for change of direction	< 0.6 s

Safety

Halogen free	No
--------------	----

Protection	with dismantling protection
------------	-----------------------------

Use conditions

Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)

Identification

Application, usage	Blind control
Main design line	Berker K.5
Secondary design line(s)	Electronics platform, Berker K.5

Instructions

Special note text	Can be switched to orientation led by extension unit.
-------------------	---