



85656182



IP20

## KNX radio wall-transmitter 2gang flat solar quicklink, S.1, white glossy

### Technical characteristics

#### Functions

ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value
Function	reset function (to factory setting) ; easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control
Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

#### Controls and indicators

Operation	operating areas configurable as one or two-area operation
Button / push-button	with configuration button

#### Connectivity

Radio protocol	KNX Radio
Receiver category	2

#### Voltage

Voltage	power supply via solar cells
---------	------------------------------

#### Dimensions

Assembling height	14 mm
-------------------	-------

#### Frequency

Radio transmission frequency	868.3 MHz
------------------------------	-----------

#### Power

Radio transmission power	< 10 mW
--------------------------	---------

#### Battery

Battery service life [years]	≈ 5
------------------------------	-----

#### Materials

Colour of design line	white
RAL colour	RAL 1013 - Oyster white
Material	thermoplastic
Surface appearance	glossy

#### LED control

LED	with configuration LED ; with transmission status LED, red/green/orange
-----	---

#### Installation, mounting

Subject to technical modifications

Installation mode

for flat surface mounting and extension of combinations

---

### Connection

---

Bus connection integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system

---

### Settings

---

Programming toolless quicklink configuration using buttons and LED display ; top and bottom operating areas are freely configurable

---

### Equipment

---

Number of radio channels 4

---

Number of quicklink links max. 20 transmitter/receiver

---

Transmitter duty cycle 1 %

---

Required Ø brightness at least 300 lx 6 h/day

---

### Safety

---

REACH conform No

---

RoHS conform Yes

---

Halogen free No

---

Protection with dismantling protection

---

### Use conditions

---

Operating temperature -5...45 °C

---

Energy-saving low intrinsic energy requirement

---

Relative humidity (without condensation) 0...65 % (without condensation)

---

### Identification

---

Application, usage KNX radio- operating systems

---

Main design line Berker S.1/B.3/B.7

---

Secondary design line(s) Electronics platform ; Berker S.1 ; Berker B.3 ; Berker B.7