



85320101

Extension unit for motion det., 1930/R.classic

Technical characteristics

Main electrical features

Frequency 50/60 Hz

Voltage

Operating voltage 230 V AC

Fuse

Fuse short-circuit and overload proof (electronic fuse)

Dimensions

Insertion depth 32 mm

Materials

Material / surface no conductive connection between supporting ring and spreading claws

Connection

Screw terminals (max.) 2 x 1,5/1 x 2,5 mm²

Number of motion detector extension units unlimited

Type of connection with screw terminals

Cable

Cable length, extensions max. 50 m

Use conditions

Operating temperature -5...45 °C

Energy-saving low intrinsic energy requirement

Relative humidity (without condensation) 0...65 % (without condensation)

Identification

Application, usage Motion detector

Main design line Electronics platform