



85320101

Extension unit for motion det., 1930/R.classic

Technical characteristics

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Operating voltage	230 V AC
-------------------	----------

Fuse

Fuse	short-circuit and overload proof (electronic fuse)
------	--

Dimensions

Insertion depth	32 mm
-----------------	-------

Materials

Material / surface	no conductive connection between supporting ring and spreading claws
--------------------	--

Connection

Screw terminals (max.)	2 x 1,5/1 x 2,5 mm ²
Number of motion detector extension units	unlimited
Type of connection	with screw terminals

Cable

Cable length, extensions	max. 50 m
--------------------------	-----------

Use conditions

Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)

Identification

Application, usage	Motion detector
Main design line	Electronics platform