



85656226



IP20

**KNX radio wall-transmitter 2gang flat quicklink, Q.x, ant. velvety, lacq.**

**Technical characteristics**

**Functions**

ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value
Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

**Connectivity**

Radio protocol	KNX Radio
Receiver category	2

**Dimensions**

Assembling height	14 mm
-------------------	-------

**Frequency**

Radio transmission frequency	868.3 MHz
------------------------------	-----------

**Power**

Radio transmission power	< 10 mW
--------------------------	---------

**Battery**

Battery service life [years]	≈ 5
------------------------------	-----

**Materials**

Colour of design line	anthracite
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	velvety

**Equipment**

Number of radio channels	4
Number of quicklink links	max. 20 transmitter/receiver
Transmitter duty cycle	1 %

**Safety**

Protection	with dismantling protection
------------	-----------------------------

**Use conditions**

Operating temperature	-5...45 °C
Relative humidity (without condensation)	0...65 % (without condensation)

**Identification**

---

Application, usage	KNX radio- operating systems
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

---