



85656273



IP20

KNX radio wall-transmitter 2gang flat quicklink, K.5, stainl. steel matt, lacq.

Technical characteristics

Functions

ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value
Function	reset function (to factory setting), easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control
Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

Controls and indicators

Operation	operating areas configurable as one or two-area operation
Button / push-button	with configuration button

Connectivity

Radio protocol	KNX Radio
Receiver category	2

Dimensions

Assembling height	14 mm
-------------------	-------

Frequency

Radio transmission frequency	868.3 MHz
------------------------------	-----------

Power

Radio transmission power	< 10 mW
--------------------------	---------

Battery

Battery service life [years]	≈ 5
Battery / storage battery	with lithium coin cell battery 3 V type: CR 2430

Materials

Colour of design line	stainless steel
RAL colour	RAL 9022 - Pearl light grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	matt

LED control

LED	with configuration LED, with transmission status and battery status LED, red/green/orange
-----	---

Installation, mounting

Installation mode	for flat surface mounting and extension of combinations	
Connection		
Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system	
Settings		
Programming	toolless quicklink configuration using buttons and LED display, top and bottom operating areas are freely configurable	
Equipment		
Number of radio channels		4
Number of quicklink links	max. 20 transmitter/receiver	
Transmitter duty cycle		1 %
Safety		
REACH conform		No
Protection	with dismantling protection	
Use conditions		
Operating temperature		-5...45 °C
Energy-saving	low intrinsic energy requirement	
Relative humidity (without condensation)	0...65 % (without condensation)	
Identification		
Application, usage	KNX radio- operating systems	
Main design line		Berker K.5
Secondary design line(s)	Berker.Net, Berker K.5	