



85745239



IP20



KNX radio timer quicklink, display, R.1/R.3/1930/R.cl., p. white glossy

Technical characteristics

Functions

Astronomic time shift	± 2 h
Random number generator	± 15 mn

ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, scene loading, time dimming value, push-button, status display
--------------------------	----------------------------------------------------------------------------------------------------------------------------

Function	reset function (to factory setting) ; Configurable transmission and/or reception behaviour ; Party function, no execution of automatic, radio and extension unit commands (switch protection) ; with keylock ; easy additional functions: +6 scenes, dimming, 1 up/down button control, priority
----------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Quicklink functions	quicklink functions: switching, 2 scenes, time switching, NO contact push-button, forced control
---------------------	--------------------------------------------------------------------------------------------------

Slide switch	with switchover manual/automatic mode
--------------	---------------------------------------

Power reserve	≈ 8 h
---------------	-------

Controls and indicators

Indication / display	LC display illuminated during operation ; indication of the application module/insert compatibility in the display ; LC display contrast is adjustable
----------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------

Connectivity

Radio protocol	KNX Radio
----------------	-----------

Dimensions

Width of rail mounted device (RMD)	0 modules
------------------------------------	-----------

Diameter	58 mm
----------	-------

Power

Radio transmission power	< 10 mW
--------------------------	---------

Measurement

Running accuracy	± 3 min/year
------------------	--------------

Battery

Power reserve [years]	0 a
-----------------------	-----

Materials

Colour of design line	polar white
-----------------------	-------------

Surface appearance	glossy
--------------------	--------

Connection

Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
----------------	----------------------------------------------------------------------------------

Settings

Programs	astro programme for sunrise/sundown switching with city/country or co-ordinate input, individually adaptable ; standalone programme, radio and extension unit commands are not executed ; holiday programme for random variation of the switching times in automatic operation
Time	with automatic summer-/winter time switching (can be switched off)

Equipment

Number of radio channels	1
Number of quicklink links	max. 20 transmitter/receiver
Number of switching times for on/off	20
Cylinder	2 independent preset programme memories, individually adaptable

Use

Differentiation characteristic 2 - Sales	with display
------------------------------------------	--------------

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)

Identification

Application, usage	Light control ; KNX radio- operating systems
Main design line	Berker R.1/R.3/R.8/Serie 1930/R.classic
Secondary design line(s)	Electronics platform ; Berker R.1 ; Berker R.3 ; Serie 1930 ; Series R.classic

Instructions

Special note text	Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!
-------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------