



85745289



IP20

KNX radio timer quicklink, display, S.1/B.3/B.7, p. white glossy

Technical characteristics

Functions

Astronomic time shift	± 2 h
Random number generator	± 15 mn
ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, scene loading, time dimming value, push-button, status display
Function	with keylock
Quicklink functions	quicklink functions: switching, 2 scenes, time switching, NO contact push-button, forced control
Slide switch	with switchover manual/automatic mode
Power reserve	≈ 8 h

Connectivity

Radio protocol	KNX Radio
----------------	-----------

Dimensions

Width of rail mounted device (RMD)	0 modules
------------------------------------	-----------

Power

Radio transmission power	< 10 mW
--------------------------	---------

Measurement

Running accuracy	± 3 min/year
------------------	--------------

Battery

Power reserve [years]	0 a
-----------------------	-----

Materials

Colour of design line	polar white
Material	thermoplastic

Settings

Time	with automatic summer-/winter time switching (can be switched off)
------	--

Equipment

Number of radio channels	1
Number of quicklink links	max. 20 transmitter/receiver
Number of switching times for on/off	20

Use

Differentiation characteristic 2 - Sales	with display
--	--------------

Safety	
Protection index IP	IP20
REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection
Use conditions	
Operating temperature	-5...45 °C
Relative humidity (without condensation)	0...65 % (without condensation)
Identification	
Application, usage	Light control, KNX radio- operating systems
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7