



936552568

Series switch, common input terminal, Integro - Design Flow/Pure, chr m, lacq

Technical characteristics

Architecture

Type of control unit double rocker

Configuration

Switch mode series

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

Dimensions

Depth 25 mm

Height 55.5 mm

Width 55.5 mm

Materials

Colour aluminium optics

RAL colour RAL 9006 - White aluminium

Material thermoplastic

Surface appearance matt

Connection

Type of connection with screw terminals

Type of connection Screw connection

Equipment

Lighting without lighting (cannot be illuminated)

Heating switch No

Use cases

Application Light control

Safety

Protection index IP IP20

Identification

Appliance switch type

No

Secondary design line(s)

Berker Integro Flow, Berker Integro Pure