



85342139

**Motion det. 2.2 m, R.1/R.3/1930/R.cl., p. white glossy**

**Technical characteristics**

**Architecture**

Fixing mode flush-mounting

**Functions**

Function with keylock

**Controls and indicators**

Button / push-button with button for on/off/automatic

**Dimensions**

Assembling height 34 mm

Nominal mounting height 2.2 m

Diameter 57.6 mm

**Measurement**

Detection field, rectangular shaped  $\approx 8 \times 12$  m

**Reach distance**

Range, frontal  $\approx 8$  m

Range, side each  $\approx 6$  m

**Detection**

Number of detection levels 3

Detection angle, settable each side  $\approx 45 \dots 90^\circ$

Detection field  $\varnothing$ , on floor 0 m

**Materials**

Colour of design line polar white

Colour polarwhite

Material thermoplastic

**Lighting control**

Response brightness, adjustable  $\approx 5 \dots 1000$  lx , daytime operation

**Settings**

Response value luminosity adjustable Yes

Response value sensitivity adjustable Yes

Response sensitivity, settable 10...100 %

Delay time  $\approx 180$  s

Switch-off pre-warning to dimming value 50% for 30 s

**Safety**

---

Protection index IP	IP20
---------------------	------

---

Protection	with dismantling protection
------------	-----------------------------

**Use conditions**

---

Operating temperature	-5...45 °C
-----------------------	------------

---

Relative humidity (without condensation)	0...65 % (without condensation)
--	---------------------------------

**Identification**

---

Application, usage	Motion detector
--------------------	-----------------

---

Main design line	Berker R.1/R.3/R.8/Serie 1930/R.classic
------------------	---

---

Secondary design line(s)	Motion detector, Berker R.1, Berker R.3, Berker R.8
--------------------------	---

**Instructions**

---

Special note text	Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!
-------------------	--