



AD970B

RCBO 1P+N 6kA C-20A 30mA AC Class

Technical characteristics

Architecture

Neutral position	right
Number of protected poles	1
Number of poles	2 P
Type of pole	1P+N
Curve	C

Configuration

Number of modules	2
-------------------	---

Connectivity

Top connection alignment for modular devices	Aligned terminal
	
	
	
	
	
	
	
	
	
	

Main electrical features

Rated short circuit breaking capacity Icn AC according IEC60898-1	6 kA
Rated operational voltage Ue	240 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
Max operating voltage	240 V
Rated impulse withstand voltage	4 kV

Electric current

Rated residual operating current	30 mA
Rated current	20 A
Withstand not tripping on 8-20 μ s wave	250 A
Breaking and opening capacity	6 kA
min/maxi threshold value of the AC thermal operation	1.13 / 1.45 I_n
Magnetic regulating current	5 / 10 I_n
Rated short circuit breaking capacity I_{cn} under 230V AC according IEC60898-1	6 kA
Rated ultimate short-circuit breaking capacity I_{cu} under 230V AC IEC 60947-2	6 kA
Rated ultimate short-circuit breaking capacity I_{cu} under 240V AC IEC 60947-2	6 kA

Electric current / temperature

Rating current -25°C	22.7 A
----------------------	--------

Rating current -20°C	22.5 A
Rating current -15°C	22.2 A
Rating current -10°C	22 A
Rating current -5°C	21.8 A
Rating current 0°C	21.5 A
Rating current 5°C	21.3 A
Rating current 10°C	21 A
Rating current 15°C	20.8 A
Rating current 20°C	20.5 A
Rating current 25°C	20.3 A
Rating current 30°C	20 A
Rating current 35°C	19.8 A
Rating current 40°C	19.6 A
Rating current 45°C	19.4 A
Rating current 50°C	19.2 A
Rating current 55°C	19 A
Rating current 60°C	18.8 A

Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	0.95
Correction factor of rating current for 4 and 5 devices placed side-by-side	0.9
Correction factor of rating current for 6 devices placed side-by-side	0.85

Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	35 mm

Frequency

Frequency	50 Hz
-----------	-------

Selectivity

Maximal rating current of downstream aM fuse for selectivity on short-circuit	4 A
Maximal rating current of downstream gL fuse for selectivity on short-circuit	12 A
Minimal rating current of upstream aM fuse for selectivity on short-circuit	25 A
Minimal rating current of upstream gL fuse for selectivity on short-circuit	32 A

Power

Total power loss under IN	6.6 W
Power loss per pole at In	4.8 W

Tripping

Protected against nuisance tripping	No
-------------------------------------	----

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

Installation, mounting

Tightening torque	2,1Nm
-------------------	-------

Connection

Connection cross-section at output with screw, for flexible conductor	1 / 16 mm ²
Connection cross-section at output with screw, for massive conductor	1 / 25 mm ²
Connection cross-sect. flexible conductor	1 / 16mm ²
Connection cross-sect. rigid cable	1 / 25mm ²
Connection cross-section for rigid conductor, upstream terminals with screws	1 / 25 mm ²
Connection cross-section of the access with screws, with flexible conductor	1 / 16 mm ²

Standards

Standard text	IEC 61009-1
European directive WEEE	concerned

Safety

Residual current type	AC
REACH conform	No
Halogen free	No

Use conditions

Operating temperature	-25...40 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I ² t	3
Altitude	2000 m
Air humidity protection	for all climates
Storage/transport temperature	-25...70 °C

temperatur

Temperature of calibration	30 °C
----------------------------	-------