



AD975B

## RCBO 1P+N 6kA C-25A 30mA AC Class

### Technical characteristics

#### Architecture

Neutral position	right
Number of protected poles	1
Number of poles	2 P
Curve	C

#### Configuration

Number of modules	2
-------------------	---

#### Connectivity

Top connection alignment for modular devices	Aligned terminal
--	------------------

#### Main electrical features

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	6 kA
Rated operational voltage $U_e$	240 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	500 V
Max operating voltage	240 V
Rated impulse withstand voltage	4000 V

#### Electric current

Rated residual operating current	30 mA
Rated current	25 A
Withstand not tripping on 8-20 $\mu$ s wave	250 A
Breaking and opening capacity	6 kA
min/maxi threshold value of the AC thermal operation	1.13 / 1.45 $I_n$
Magnetic regulating current	5 / 10 $I_n$
Rated short circuit breaking capacity $I_{cn}$ under 230V AC according IEC60898-1	6 kA
Rated ultimate short-circuit breaking capacity $I_{cu}$ under 230V AC IEC 60947-2	6 kA
Rated ultimate short-circuit breaking capacity $I_{cu}$ under 240V AC IEC 60947-2	6 kA

#### Electric current / temperature

Rating current -25°C	28.2 A
Rating current -20°C	27.9 A

Rating current -15°C	27.6 A
Rating current -10°C	27.4 A
Rating current -5°C	27.1 A
Rating current 0°C	26.8 A
Rating current 5°C	26.5 A
Rating current 10°C	26.2 A
Rating current 15°C	25.9 A
Rating current 20°C	25.6 A
Rating current 25°C	25.3 A
Rating current 30°C	25 A
Rating current 35°C	24.8 A
Rating current 40°C	24.5 A
Rating current 45°C	24.3 A
Rating current 50°C	24 A
Rating current 55°C	23.8 A
Rating current 60°C	23.5 A

#### Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	0.95
Correction factor of rating current for 4 and 5 devices placed side-by-side	0.9
Correction factor of rating current for 6 devices placed side-by-side	0.85

#### Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	35 mm

#### Frequency

Frequency	50 Hz
-----------	-------

#### Selectivity

Maximal rating current of downstream aM fuse for selectivity on short-circuit	6 A
Maximal rating current of downstream gL fuse for selectivity on short-circuit	12 A
Minimal rating current of upstream aM fuse for selectivity on short-circuit	25 A
Minimal rating current of upstream gL fuse for selectivity on short-circuit	32 A

#### Power

Total power loss under I <sub>N</sub>	9.3 W
Power loss per pole at I <sub>N</sub>	5.9 W

#### Tripping

Protected against nuisance tripping	No
-------------------------------------	----

#### Endurance

Subject to technical modifications

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

#### Connection

Connection cross-section at output with screw, for flexible conductor	1 / 16 mm <sup>2</sup>
Connection cross-section at output with screw, for massive conductor	1 / 25 mm <sup>2</sup>
Connection cross-sect. flexible conductor	1 / 16mm <sup>2</sup>
Connection cross-section for rigid conductor, upstream terminals with screws	1 / 25 mm <sup>2</sup>
Connection cross-section of the access with screws, with flexible conductor	1 / 16 mm <sup>2</sup>

#### Standards

Standard text	IEC 61009-1
European directive WEEE	concerned

#### Safety

Protection index IP	IP20
Residual current type	AC
REACH conform	No
Halogen free	No

#### Use conditions

Operating temperature	-25...40 °C
Class of energy limitation I <sup>2</sup> t	3
Altitude	2000 m
Storage/transport temperature	-25...70 °C

#### temperatur

Temperature of calibration	30 °C
----------------------------	-------