



85342224

**IR motion detector comfort 2.2 m, Q.x alu velvety, lacquered**

**Technical characteristics**

**Functions**

Mode of operation	μ-processor controlled mode of operation
Function	Teach function for response brightness via button ; with keylock ; Party function for switching on for 2 hours ; with memory function for presence simulation
Operating mode	step operation with immunity time (e.g. for stair light/impact current circuits)

**Controls and indicators**

Button / push-button	with button for on/off/automatic
----------------------	----------------------------------

**Dimensions**

Assembling height	34 mm
Nominal mounting height	2.2 m

**Tripping**

immunity time	≈ 10 s
---------------	--------

**Measurement**

Detection field, rectangular shaped	≈ 8 x 12 m
-------------------------------------	------------

**Reach distance**

Range, frontal	≈ 8 m
Range, side	each ≈ 6 m

**Detection**

Number of detection levels	3
Detection angle, settable	each side ≈ 45...90 °
Detection field Ø, on floor	0 m

**Materials**

Colour of design line	aluminium
Material / workmanship	lacquered

**Lighting control**

Response brightness, adjustable	≈ 5...1000 lx , daytime operation
---------------------------------	-----------------------------------

**LED control**

LED	with operation and status LED, red/green/orange ; LED application module/insert compatibility display
-----	---

**Settings**

Response value luminosity adjustable	Yes
--------------------------------------	-----

Response value sensitivity adjustable	Yes
Response sensitivity, settable	10...100 %
Short time mode	200 ms
Delay time	≈ 180 s
Delay time, adjustable	≈ 10 s...30 mn
Switch-off pre-warning to dimming value 50% for	30 s

### Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection

### Use conditions

Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)

### Identification

Application, usage	Light control ; Motion detector
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

### Instructions

Information text	Continuous direct sunlight penetrating the upward-pointing detection plane can result in failure of the motion detector. Only suitable for indoor areas!
------------------	--