



AF132Z

**RCBO electronic 1P 6kA C-32A 300mA type AC**

**Technical characteristics**

**Architecture**

Neutral position	right
Number of protected poles	1
Number of poles	1 P
Curve	C

**Functions**

Concurrently switching N-neutral	No
----------------------------------	----

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	6 kA
Rated operational voltage $U_e$	230 / 240 V
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	250 V
Max operating voltage	253 V
Rated impulse withstand voltage	4000 V

**Electric current**

Rated residual operating current	300 mA
Rated current	32 A
Breaking and opening capacity	6 kA
min/maxi threshold value of the AC thermal operation	1.13 / 1.45 $I_n$
Magnetic regulating current	5 / 10 $I_n$
Rated short circuit breaking capacity $I_{cn}$ under 230V AC according IEC60898-1	6 kA

**Electric current / temperature**

Rating current -25°C	40.06 A
Rating current -20°C	39.39 A
Rating current -15°C	38.72 A
Rating current -10°C	38.03 A
Rating current -5°C	37.33 A
Rating current 0°C	36.62 A
Rating current 5°C	35.89 A

Rating current 10°C	35.14 A
Rating current 15°C	34.39 A
Rating current 20°C	33.61 A
Rating current 25°C	32.81 A
Rating current 30°C	32 A
Rating current 35°C	31.16 A
Rating current 40°C	30.31 A
Rating current 45°C	29.42 A
Rating current 50°C	28.51 A
Rating current 55°C	27.57 A
Rating current 60°C	26.6 A

#### Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	0.95
Correction factor of rating current for 4 and 5 devices placed side-by-side	0.9
Correction factor of rating current for 6 devices placed side-by-side	0.85

#### Dimensions

Depth of installed product	70 mm
Height of installed product	115 mm
Width of installed product	17.5 mm

#### Frequency

Frequency	50 to 60 Hz
-----------	-------------

#### Power

Total power loss under IN	9.63 W
Power loss per pole at In	5.53 W

#### Tripping

Protected against nuisance tripping	No
-------------------------------------	----

#### Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

#### Connection

Connection cross-section at output with screw, for flexible conductor	1 / 16 mm <sup>2</sup>
Connection cross-section at output with screw, for massive conductor	1 / 25 mm <sup>2</sup>
Connection cross-section for rigid conductor, upstream terminals with screws	1 / 25 mm <sup>2</sup>
Connection cross-section of the access with screws, with flexible conductor	1 / 16 mm <sup>2</sup>

#### Standards

Standard text	IEC 61009-1 ; EN 61009-1
---------------	--------------------------

<b>Safety</b>	
Protection index IP	IP20
Residual current type	AC
<b>Use conditions</b>	
Class of energy limitation I <sup>2</sup> t	3
Altitude	2000 m