



85342275

IR motion detector comfort 2.2 m, K.1, anthracite matt, lacquered

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

Mode of operation	μ-processor controlled mode of operation
-------------------	--

Function	Teach function for response brightness via button, with keylock, Party function for switching on for 2 hours, with memory function for presence simulation
----------	--

Operating mode	step operation with immunity time (e.g. for stair light/impact current circuits)
----------------	--

Controls and indicators

Button / push-button	with button for on/off/automatic
----------------------	----------------------------------

Dimensions

Assembling height	34 mm
-------------------	-------

Nominal mounting height	2.2 m
-------------------------	-------

Tripping

immunity time	≈ 10 s
---------------	--------

Measurement

Detection field, rectangular shaped	≈ 8 x 12 m
-------------------------------------	------------

Reach distance

Range, frontal	≈ 8 m
----------------	-------

Range, side	each ≈ 6 m
-------------	------------

Detection

Number of detection levels	3
----------------------------	---

Detection angle, settable	each side ≈ 45...90 °
---------------------------	-----------------------

Detection field Ø, on floor	0 m
-----------------------------	-----

Materials

Colour of design line	anthracite
-----------------------	------------

Colour	anthracite
--------	------------

Material / workmanship	lacquered
------------------------	-----------

Material	thermoplastic
----------	---------------

Lighting control

Response brightness, adjustable	≈ 5...1000 lx , daytime operation
---------------------------------	-----------------------------------

LED control

LED

with operation and status LED, red/green/orange,
LED application module/insert compatibility display**Settings**

Response value luminosity adjustable	Yes
Response value sensitivity adjustable	Yes
Response sensitivity, settable	10...100 %
Short time mode	200 ms
Delay time	≈ 180 s
Delay time, adjustable	≈ 10 s...30 mn
Switch-off pre-warning to dimming value 50% for	30 s

Safety

Protection index IP	IP20
REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)

Identification

Application, usage	Light control, Motion detector
Main design line	Berker K.1
Secondary design line(s)	Motion detector, Berker K.1