



85345182



IP20

## KNX radio motion det. comf 1.1 m quicklink, S.1, white glossy

### Technical characteristics

#### Functions

Mode of operation	μ-processor controlled mode of operation
ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value, brightness display, movement scene loading, no movement scene loading
Function	reset function (to factory setting) ; Party function for switching on for 2 hours ; with memory function for presence simulation ; with keylock ; Switch-off pre-warning on dimmer inserts ; Teach function for response brightness via button
Light scenes	scene opening via KNX radio appliances ; scene saving lockable
Quicklink functions	quicklink functions: switching, dimming, 2 scenes, time switching, NO contact push-button, Memory, forced control, Master-Slave

#### Compatibility

Extension unit	optional operation of extension units using installation push-button
----------------	--

#### Controls and indicators

Operation	remote control via quicklink transmitter
Button / push-button	with configuration and function button ; with button for on/off/automatic/memory/party function

#### Connectivity

Radio protocol	KNX Radio
Receiver category	2

#### Dimensions

Assembling height	34 mm
Nominal mounting height	1.1 m

#### Frequency

Radio transmission frequency	868.3 MHz
------------------------------	-----------

#### Power

Radio transmission power	< 10 mW
--------------------------	---------

#### Measurement

Detection field, rectangular shaped	≈ 12 x 16 m
-------------------------------------	-------------

#### Reach distance

Range, frontal	≈ 12 m
Range, side	each ≈ 8 m

<b>Detection</b>	
Number of detection levels	2
Detection angle, settable	each side $\approx 45 \dots 90^\circ$
<b>Materials</b>	
Colour of design line	white
Surface appearance	glossy
<b>Lighting control</b>	
Response brightness, adjustable	$\approx 5 \dots 1000$ lx , daytime operation
<b>LED control</b>	
LED	LED application module/insert compatibility display ; with configuration and function LEDs ; with operation and status LED, red/green/orange
<b>Connection</b>	
Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
<b>Settings</b>	
Response sensitivity, settable	10...100 %
Delay time, adjustable	$\approx 1 \text{ s} \dots 3 \text{ h}$
Switch-off pre-warning to dimming value 50% for	30 s
<b>Equipment</b>	
Number of radio channels	1
Number of quicklink links	max. 20 transmitter/receiver
Transmitter duty cycle	1 %
<b>Safety</b>	
REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection
<b>Use conditions</b>	
Operating temperature	$-5 \dots 45^\circ\text{C}$
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)
<b>Identification</b>	
Application, usage	Motion detector ; KNX radio- sensors
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Electronics platform ; Berker S.1 ; Berker B.3 ; Berker B.7
<b>Instructions</b>	
Information text	Continuous direct sunlight penetrating the upward-pointing detection plane can result in failure of the motion detector. Only suitable for indoor areas!