



85421700

DALI/DSI control insert, electronics

Technical characteristics

Architecture

Type of control unit	Push button
----------------------	-------------

Functions

Switching	for switching and controlling electr. ballasts and Tronic transformer with DALI/DSI interface
-----------	-----------------------------------------------------------------------------------------------

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Operating voltage	230 V AC
DALI voltage	16 V DC

Electric current

Control current	40 mA
Output current	max. 40 mA

Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	32 mm
Claw guidance installation depth	32 mm
Housing installation depth	22 mm

Power

Power consumption (standby)	< 0.4 W
-----------------------------	---------

Measurement

Extension unit input	with extension unit input for push-button (NO contact)
----------------------	--------------------------------------------------------

Materials

Colour	white
--------	-------

Connection

Quantity of DALI devices	max. 20
Type of connection	with screw terminals
Number of substations	unlimited

Cable

DALI cable length at 1.5 mm ²	max. 300 m
Cable length, extensions	max. 100 m

Equipment	
Substation input	Yes
Number of DALI/DSI devices, passive operation	max. 64
Brightness	switch-on brightness level can be stored safe after power failure
DALI	Bus communication in Broadcast mode according to IEC 62386-102
Safety	
REACH conform	No
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-5...45 °C
Storage/transport temperature	-20...60 °C
Relative humidity (without condensation)	0...65 % (without condensation)
Identification	
Application, usage	Light control, KNX radio- operating systems