



85648175



IP20

quicklink

## KNX radio button 4gang quicklink, K.1, ant. matt, lacq.

### Technical characteristics

#### Functions

ETS additional functions	ETS additional functions: +6 scenes, 1 button control up/down, operating mode on/off, dimming value, brightness display, push-button, status display, forced control
--------------------------	--

Function	Functions for the push-button operation areas up/down or left/right can be freely configured as receiver for controlling the connected load and as transmitter for remote control of a blind, for example ; reset function (to factory setting) ; Configurable transmission and/or reception behaviour
----------	--

Light scenes	scene saving lockable
--------------	-----------------------

Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory
---------------------	--

#### Controls and indicators

Operation	operating areas configurable as one or two-area operation
-----------	---

Button / push-button	with configuration and function button
----------------------	--

#### Connectivity

Radio protocol	KNX Radio
----------------	-----------

Receiver category	2
-------------------	---

#### Power

Radio transmission power	< 10 mW
--------------------------	---------

#### Materials

Colour of design line	anthracite
-----------------------	------------

Material / workmanship	lacquered
------------------------	-----------

Surface appearance	matt
--------------------	------

#### LED control

LED	with configuration and function LEDs ; LED application module/insert compatibility display
-----	--

#### Connection

Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
----------------	--

#### Settings

Programming	toolless quicklink configuration using buttons and LED display
-------------	--

#### Equipment

Number of radio channels	4
--------------------------	---

Number of quicklink links	max. 20 transmitter/receiver
Transmitter duty cycle	1 %
Brightness	switch-on brightness level for each operating area on configuration with dimmer insert, power failure proof, storable
<b>Safety</b>	
REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection
<b>Use conditions</b>	
Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)
<b>Identification</b>	
Application, usage	Light control ; KNX radio- operating systems
Main design line	Berker K.1
Secondary design line(s)	Berker.Net ; Berker K.1
<b>Instructions</b>	
Information text	Extended operating options on 1gang inserts through 2 additional, freely-configurable radio channels.