



85648175



IP20

KNX radio button 4gang quicklink, K.1, ant. matt, lacq.

Technical characteristics

Functions

| | |
|--------------------------|--|
| ETS additional functions | ETS additional functions: +6 scenes, 1 button control up/down, operating mode on/off, dimming value, brightness display, push-button, status display, forced control |
| Quicklink functions | quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory |

Connectivity

| | |
|-------------------|-----------|
| Radio protocol | KNX Radio |
| Receiver category | 2 |

Power

| | |
|--------------------------|---------|
| Radio transmission power | < 10 mW |
|--------------------------|---------|

Materials

| | |
|------------------------|-----------------------|
| Colour of design line | anthracite |
| RAL colour | RAL 7021 - Black grey |
| Material / workmanship | lacquered |
| Material | thermoplastic |
| Surface appearance | matt |

Equipment

| | |
|---------------------------|------------------------------|
| Number of radio channels | 4 |
| Number of quicklink links | max. 20 transmitter/receiver |
| Transmitter duty cycle | 1 % |

Safety

| | |
|---------------|-----------------------------|
| REACH conform | No |
| RoHS conform | Yes |
| Halogen free | No |
| Protection | with dismantling protection |

Use conditions

| | |
|--|---------------------------------|
| Operating temperature | -5...45 °C |
| Relative humidity (without condensation) | 0...65 % (without condensation) |

Identification

| | |
|--------------------------|---|
| Application, usage | Light control, KNX radio- operating systems |
| Main design line | Berker K.1 |
| Secondary design line(s) | Berker K.1 |

Information text

Extended operating options on 1gang inserts
through 2 additional, freely-configurable radio
channels.