


85648189



IP20

## KNX radio button 4gang quicklink, S.1/B.3/B.7, p. white glossy

### Technical characteristics

#### Functions

ETS additional functions	ETS additional functions: +6 scenes, 1 button control up/down, operating mode on/off, dimming value, brightness display, push-button, status display, forced control
--------------------------	--

Function	Functions for the push-button operation areas up/down or left/right can be freely configured as receiver for controlling the connected load and as transmitter for remote control of a blind, for example, reset function (to factory setting), Configurable transmission and/or reception behaviour
----------	--

Light scenes	scene saving lockable
--------------	-----------------------

Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory
---------------------	--

#### Controls and indicators

Operation	operating areas configurable as one or two-area operation
Button / push-button	with configuration and function button

#### Connectivity

Radio protocol	KNX Radio
Receiver category	2

#### Power

Radio transmission power	< 10 mW
--------------------------	---------

#### Materials

Colour of design line	polar white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic

#### LED control

LED	with configuration and function LEDs, LED application module/insert compatibility display
-----	---

#### Connection

Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
----------------	--

#### Settings

Programming	toolless quicklink configuration using buttons and LED display
-------------	--

#### Equipment

Number of radio channels	4
Number of quicklink links	max. 20 transmitter/receiver
Transmitter duty cycle	1 %
Brightness	switch-on brightness level for each operating area on configuration with dimmer insert, power failure proof, storable
<b>Safety</b>	
REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection
<b>Use conditions</b>	
Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)
<b>Identification</b>	
Application, usage	Light control, KNX radio- operating systems
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Electronics platform, Berker S.1, Berker B.3, Berker B.7
<b>Instructions</b>	
Information text	Extended operating options on 1gang inserts through 2 additional, freely-configurable radio channels.