



CZ001

Auxiliary contact for RCCB 2(1C+1O) 6A 240V AC

Technical characteristics

Architecture

Fixing mode	Clipped
-------------	---------

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage U_e	230 / 440 V
---------------------------------	-------------

Frequency	50 Hz
-----------	-------

Voltage

Rated insulation voltage	500 V
--------------------------	-------

Rated operational voltage in DC	12 / 250 V
---------------------------------	------------

Electric current

Acceptable current rating with AC1	6 A
------------------------------------	-----

Rated current	6 A
---------------	-----

$I_{min} = f(U = 230 \text{ V AC})$	6 A
-------------------------------------	-----

$I_{min} = f(U = 230 \text{ V DC})$	0.6 A
-------------------------------------	-------

$I_{min}=f(U=400\text{V AC})$ for power circuit	3 A
---	-----

Dimensions

Width of installed product	18 mm
----------------------------	-------

Power

Total power loss under I_N	0.1 W
------------------------------	-------

Endurance

Electric endurance in number of cycles	6000
--	------

Number of mechanical operations	12000
---------------------------------	-------

Installation, mounting

Factory fitted	No
----------------	----

Equipment

Quantity of NC contacts	1
-------------------------	---

Quantity of NO contacts	1
-------------------------	---

Quantity of INV contacts	0
--------------------------	---

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-25...60 °C
Storage/transport temperature	-40...80 °C
