



DR32S



Din rail board, 2 row 32M, non-transparent door, surface

Technical characteristics

Architecture

Intended door position	left
------------------------	------

Configuration

Number of modules	32
-------------------	----

Compatibility

Suitable for lightning protection	Yes
-----------------------------------	-----

Dimensions

Insertion depth	110 mm
-----------------	--------

Depth of installed product	115 mm
----------------------------	--------

Internal depth	107 mm
----------------	--------

Height of installed product	474 mm
-----------------------------	--------

Installation height	470 mm
---------------------	--------

Width of installed product	405 mm
----------------------------	--------

Width in division units	16
-------------------------	----

Thickness of sidewall material	1.2 mm
--------------------------------	--------

Cover, door

Material thickness cover	1.2 mm
--------------------------	--------

Identification of protection index	40
------------------------------------	----

Interlockable	No
---------------	----

Number of keylock of the door	0
-------------------------------	---

Cover type	Closed (plain)
------------	----------------

Door leave	single
------------	--------

Cover type	Cover
------------	-------

Transparent cover or door	No
---------------------------	----

Materials

Copper weight of the product	0 kg
------------------------------	------

Colour	light grey
--------	------------

Material quality	Steel
------------------	-------

Surface appearance	matt
--------------------	------

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Suitable for ground mounting	No
------------------------------	----

Settings

Equipment

Number of rows	2
Number of keys	1
Quantity of rails	2
On/Off switch	No
Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	Yes
Earthing terminal block	No
Neutral terminal block	Yes

Standards

Approvals	BS EN 61439-3
European directive WEEE	not concerned

Safety

IK protection code against mechanical impacts	IK05
Protection class	isol.class I
Glow wire test	according to IEC 61439-1
RoHS conform	Yes
Halogen free	No
Fire resistance	-