



EC360

3Ph Kwhmeter direct 100A

Technical characteristics

Architecture

Number of poles	3 P
Type of pole	3P+N
Fixing mode	REG

Functions

Tarif type	One-tariff
------------	------------

Configuration

Number of modules	7
-------------------	---

Compatibility

Suitable for	Purchase
--------------	----------

Main electrical features

Rated operational voltage Ue	195 / 400 / 460 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	4 kV
--------------------------	------

Electric current

Operating current	0.08 / 100 A
Rated current	100 A
Max. measurement circuit current	100 A

Dimensions

Height of installed product	90 mm
Width of installed product	122.5 mm

Power

Power consumed	7.5 VA
Total power loss under IN	1.8 W
Plage Impulsion/KWh	10 Imp/kWh

Electrical specifications

Type of pulse generator	électrical
-------------------------	------------

Measurement

Idle power measurement	activ and reactiv energy
Voltage measurement range	230 V

Type of measuring instrument	electronical
Power supply	
Number of phases for the power supply	4 phases
Connection	
Type of Bus connexion	other
Settings	
Value of a pulse	100 Wh
Equipment	
Tariff model of kilowatt-hour meter	Externa
Rolling code	No
Use	
Pulse duration	100 ms
Interval between 2 pulses	100 ms
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	-10...55 °C
Storage/transport temperature	-25...70 °C