



85656139



IP20

KNX radio wall-transmitter 2gang flat solar quicklink, R.1/R.3, p. white glossy

Technical characteristics

Functions

ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value
Function	reset function (to factory setting) ; easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control
Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

Controls and indicators

Operation	operating areas configurable as one or two-area operation
Button / push-button	with configuration button

Connectivity

Radio protocol	KNX Radio
Receiver category	2

Voltage

Voltage	power supply via solar cells
---------	------------------------------

Dimensions

Assembling height	14 mm
-------------------	-------

Frequency

Radio transmission frequency	868.3 MHz
------------------------------	-----------

Power

Radio transmission power	< 10 mW
--------------------------	---------

Battery

Battery service life [years]	≈ 5
------------------------------	-----

Materials

Colour of labelling	105,105,105
Colour of design line	polar white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Material for printing	ASA polar white
Surface appearance	glossy

LED control

LED

with configuration LED ; with transmission status
LED, red/green/orange

Installation, mounting

Installation mode for flat surface mounting and extension of combinations

Connection

Bus connection integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system

Settings

Programming toolless quicklink configuration using buttons and LED display ; top and bottom operating areas are freely configurable

Equipment

Number of radio channels 4

Number of quicklink links max. 20 transmitter/receiver

Type of configuration Laserdruck

Transmitter duty cycle 1 %

Required Ø brightness at least 300 lx 6 h/day

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Protection with dismantling protection

Use conditions

Operating temperature -5...45 °C

Energy-saving low intrinsic energy requirement

Relative humidity (without condensation) 0...65 % (without condensation)

Identification

Application, usage KNX radio- operating systems

Main design line Berker R.1/R.3/R.8

Secondary design line(s) Berker.Net ; Berker R.1 ; Berker R.3 ; Berker R.8