



ECN140D



## 1 Phase kWhmeter direct 40A 1M

### Technical characteristics

#### Architecture

Number of poles	2 P
Fixing mode	DIN rail type O (symmetrical)

#### Functions

Tarif type	One-tariff
------------	------------

#### Configuration

Number of modules	1
-------------------	---

#### Compatibility

Suitable for	Purchase
--------------	----------

#### Main electrical features

Rated operational voltage Ue	184 / 276 V
Type of supply voltage	AC
Frequency	50 Hz

#### Voltage

Max operating voltage	300 V
Rated impulse withstand voltage	6 kV

#### Electric current

Minimum operating current	0.02 A
Operating current	0.02 / 40 A
Rated current	40 A
Reference current	5 A
Max. measurement circuit current	40 A

#### Dimensions

Depth of installed product	58 mm
Height of installed product	92 mm
Width of installed product	18 mm

#### Power

Power consumed	2 VA
Total power loss under IN	1 W

#### Electrical specifications

Type of pulse generator	optical
-------------------------	---------

**Measurement**

Frequency measuring range	45 to 65 Hz
Type of measuring instrument	electrical
Principle of measurement	Direct measurement

**Installation, mounting**

Mounting type	din-Rail
---------------	----------

**Connection**

Wire cross section of metering entrance wire	16 mm <sup>2</sup>
Wire cross section of metering outgoing wire	16 mm <sup>2</sup>

**Equipment**

Type of display	LCD
Type of counter	single-phase counter

**Standards**

Standard text	IEC 62053-21 / 23 ; IEC 61557-12
European directive WEEE	concerned

**Safety**

Protection index IP	IP20
Protection class	isol.class II

**Use conditions**

Operating temperature	-25...55 °C
Altitude	2000 m
Storage/transport temperature	-25...70 °C