



85656189



IP20

KNX radio wall-transmitter 2gang flat solar quicklink, S.1/B.3/B.7, p.white gl.

Technical characteristics

Functions

ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value
Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

Connectivity

Radio protocol	KNX Radio
Receiver category	2

Dimensions

Assembling height	14 mm
-------------------	-------

Frequency

Radio transmission frequency	868.3 MHz
------------------------------	-----------

Power

Radio transmission power	< 10 mW
--------------------------	---------

Battery

Battery service life [years]	≈ 5
------------------------------	-----

Materials

Colour of design line	polar white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic

Equipment

Number of radio channels	4
Number of quicklink links	max. 20 transmitter/receiver
Transmitter duty cycle	1 %
Required Ø brightness	at least 300 lx 6 h/day

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Relative humidity (without condensation)	0...65 % (without condensation)
Identification	
Application, usage	KNX radio- operating systems
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7