



ECP180D



1 Phase kWhmeter direct 80A 2M S0 MID

Technical characteristics

Architecture

Number of poles	2 P
Type of pole	1P+N

Functions

Precision class	B
Tarif type	T1...T2 (230 V AC) / -

Configuration

Number of modules	2
-------------------	---

Compatibility

Suitable for	Purchase / supply
--------------	-------------------

Main electrical features

Rated operational voltage Ue	92 / 276 V
Type of supply voltage	AC
Frequency	50 Hz

Voltage

Max operating voltage	300 V
Rated impulse withstand voltage	6 kV

Electric current

Minimum operating current	0.015 A
Operating current	0.015 / 80 A
Rated current	80 A
Reference current	5 A
Max. measurement circuit current	80 A

Dimensions

Depth of installed product	60 mm
Height of installed product	92 mm
Width of installed product	36 mm

Power

Power consumed	2 VA
Total power loss under IN	1 W
Plage Impulsion/KWh	1 / 1000 Imp/kWh

Electrical specifications

Measurement

Frequency measuring range	45 to 65 Hz
Type of measuring instrument	electrical
Principle of measurement	Direct measurement

Power supply

Supply voltage	230 V ± 20%
----------------	-------------

Installation, mounting

Tightening torque	2Nm
Mounting type	din-Rail

Connection

Wire cross section of metering entrance wire	33 mm ²
Wire cross section of metering outgoing wire	33 mm ²

Settings

Value of a pulse	100 Wh
------------------	--------

Equipment

Type of display	retro illuminated display
Tariff model of kilowatt-hour meter	Externa
Type of counter	single-phase counter

Use

Pulse duration	30 / 100 ms
----------------	-------------

Standards

Standard text	EN 50470-1 / 3 ; IEC 62053-21 / 23 ; IEC 61557-12
Certified product	MID (Measuring Instruments Directive)

Safety

Protection class	isol.class II
------------------	---------------

Use conditions

Operating temperature	-25...55 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Altitude	2000 m
Storage/transport temperature	-25...70 °C