



85741124

## Blind time switch Q.x alu velvety, lacquered

### Technical characteristics

#### Functions

Astronomic time shift	± 2 h
Running time	2 mn
Random number generator	± 15 mn
Function	reset function (to factory setting) ; with keylock ; Party function, no execution of automatic, radio and extension unit commands (lock-out protection)
Slide switch	with switchover manual/automatic mode
Power reserve	≈ 24 h

#### Controls and indicators

Indication / display	LC display illuminated during operation ; indication of the application module/insert compatibility in the display ; LC display contrast is adjustable
----------------------	--

#### Main electrical features

Nominal voltage	12 V
Frequency	- Hz

#### Installation, mounting

Installation mode	as devices cover for clamp cover
-------------------	----------------------------------

#### Settings

Minimum slat adjustment time	≈ 250 ms
Lamella adjustment on button-press	< 0.5 s
Programs	astro programme for sunrise/sundown switching with city/country or co-ordinate input, individually adaptable ; holiday programme for random variation of the operation times in automatic operation
Time	with automatic summer-/winter time switching (can be switched off)

#### Equipment

Number of operation times for up/down	20
Self-retaining for 2 min on button-press	> 0.5 s
Change-over time for change of direction	< 0.6 s
Cylinder	2 independent preset programme memories, individually adaptable

#### Use

Differentiation characteristic 2 - Sales	with display
--	--------------

#### Safety

REACH conform	No
---------------	----

RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection
<b>Use conditions</b>	
Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)
<b>Identification</b>	
Application, usage	Blind control
Secondary design line(s)	Electronics platform ; Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
<b>Instructions</b>	
Special note text	Can be switched to orientation led by extension unit.