




85745131



IP20



KNX radio blind time switch quicklink, display, R.1/R.3/1930/R.cl., black glossy

Technical characteristics

Functions

Astronomic time shift	± 2 h
Running time	2 mn
Random number generator for holiday program	± 15 mn
ETS additional functions	ETS additional functions: +6 scenes, operating mode, status display, 2 x alarm
Function	reset function (to factory setting) ; with keylock ; Party function, no execution of automatic, radio and extension unit commands (lock-out protection) ; Configurable transmission and/or reception behaviour ; easy additional functions: +6 scenes, 1 up/down operating mode
Light scenes	slat position storable for scene ; scene opening via KNX radio appliances
Quicklink functions	quicklink functions for integration into the individual, group and master control of blinds/shutters ; quicklink functions: blind, 2 scenes, forced control, up/down push-button
Slide switch	with switchover manual/automatic mode
Power reserve	≈ 8 h

Controls and indicators

Indication / display	indication of the application module/insert compatibility in the display ; LC display contrast is adjustable ; LC display illuminated during operation
----------------------	--

Connectivity

Radio protocol	KNX Radio
----------------	-----------

Dimensions

Width of rail mounted device (RMD)	0 modules
Diameter	58 mm

Power

Radio transmission power	< 10 mW
--------------------------	---------

Measurement

Running accuracy	± 3 min/year
------------------	--------------

Battery

Power reserve [years]	0 h
-----------------------	-----

Detection

Sensor	sun protection and twilight-controlled lowering with radio brightness sensor
--------	--

Materials

Colour of design line	black
Surface appearance	glossy

Connection

Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
----------------	--

Settings

Minimum slat adjustment time	≈ 150 ms
Lamella adjustment on signal duration	< 1 s
Lamella adjustment on button-press	< 0.5 s

Programs	astro programme for sunrise/sundown switching with city/country or co-ordinate input, individually adaptable ; standalone programme, radio and extension unit commands are not executed ; holiday programme for random variation of the operation times in automatic operation
----------	--

Time	with automatic summer-/winter time switching (can be switched off)
------	--

Equipment

Number of operation times for up/down	20/day
Number of radio channels	1
Number of quicklink links	max. 20 transmitter/receiver
Self-retaining for 2 min on signal length	> 1 s
Self-retaining for 2 min on button-press	> 0.5 s
Change-over time for change of direction	< 0.6 s

Cylinder	2 independent preset programme memories, individually adaptable
----------	---

Use

Differentiation characteristic 2 - Sales	with display
--	--------------

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)

Identification

Application, usage	Blind control ; KNX radio- operating systems
Main design line	Berker R.1/R.3/R.8/Serie 1930/R.classic
Secondary design line(s)	Electronics platform ; Berker R.1 ; Berker R.3 ; Series R.classic ; Serie 1930

Instructions

Can be switched to orientation led by extension unit.
; Note: When integrating this product into the Serie
1930, the 1gang frame for centre plate Ø 58 mm,
order no.: 1382 0... may only be used. Installation in
multiple combinations of the Serie 1930 is not
possible!

Special note text