



85745226



IP20

KNX radio timer quicklink, display, Q.x, ant. velvety, lacq.

Technical characteristics

Functions

Astronomic time shift	± 2 h
Random number generator	± 15 mn
ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, scene loading, time dimming value, push-button, status display
Function	with keylock
Quicklink functions	quicklink functions: switching, 2 scenes, time switching, NO contact push-button, forced control
Slide switch	with switchover manual/automatic mode
Power reserve	≈ 8 h

Connectivity

Radio protocol	KNX Radio
----------------	-----------

Dimensions

Width of rail mounted device (RMD)	0 modules
------------------------------------	-----------

Power

Radio transmission power	< 10 mW
--------------------------	---------

Measurement

Running accuracy	± 3 min/year
------------------	--------------

Battery

Power reserve [years]	0 a
-----------------------	-----

Materials

Colour of design line	anthracite
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	velvety

Settings

Time	with automatic summer-/winter time switching (can be switched off)
------	--

Equipment

Number of radio channels	1
Number of quicklink links	max. 20 transmitter/receiver
Number of switching times for on/off	20

Use

Differentiation characteristic 2 - Sales

with display

Safety

Protection index IP

IP20

Protection

with dismantling protection

Use conditions

Operating temperature

-5...45 °C

Relative humidity (without condensation)

0...65 % (without condensation)

Identification

Application, usage

Light control, KNX radio- operating systems

Main design line

Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s)

Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9