




EE805A



**IP21**

## Movement detector 360° flush mounted with normally open contact

### Technical characteristics

#### Functions

Function can only be used as individual unit

#### Main electrical features

Rated operational voltage  $U_e$  230 V

Frequency 50/60 Hz

#### Voltage

Operating voltage 230 V ~ +10%/-15%

#### Electric current

Switching current (ohmic) max. 10 A

#### Dimensions

Height of installed product 15.5 mm

Dimensions ( $\varnothing$  x H) 90 x 61 mm

Width of installed product 19 mm

Installation opening  $\varnothing$  75 mm

Assembling height 61 mm

Recommended installation height 2.5...3.5 m

Installation wall thickness 5...20 mm

#### Power

Halogen switching capacity 230V 0 / 2300 W

Max. power with fluo uncompensated lamps 1000 VA

Power consumption (standby) 0.3 W

Incandescent bulb power 0 / 2300 W

Maximum power per output for low-voltage halogen lamps with conv. transformer 1500 W

Conventional transformers max. 1500 VA

Electronic transformers max. 1500 W

#### Power supply

Supply voltage 230 V +10% / -15%

#### Detection

Detection angle 360 °

Detection field  $\varnothing$ , on floor  $\approx$  6 m

#### Materials

Colour white

**Lighting control**

Response brightness, adjustable	≈ 5...1000 lx
Brightness measurement range	5 / 1000 Lux
Fluorescent lamps with electronical ballast (EB)	8 x 58 W

**Fluorescent bulbs control**

Energy-saving lamps	10 x 20 W
Fluorescent lamps uncompensated	1000 W

**LED control**

230V LED lamps	20 x 20 W
----------------	-----------

**Incandescent bulbs control**

12 V halogen lamps	1500 VA
--------------------	---------

**Installation, mounting**

Maximum Mounting Height	4 m
Mounting type	flush-mounted
Installation mode	for ceiling mounting ; with spring clips for ceiling installation

**Connection**

Conductor cross-section	1...2.5 mm <sup>2</sup>
Type of contacts	Normally open contact (NO)
Type of connection	with plug-in terminals

**Settings**

Response value sensitivity adjustable	No
Delay time, adjustable	5 s...30 mn
Setting	with potentiometers for setting the response brightness and delay time

**Scope of delivery**

Component	with fitting material
-----------	-----------------------

**Equipment**

Potential-free	not potential-free
----------------	--------------------

**Safety**

Protection class	isol.class II
------------------	---------------

**Use conditions**

Operating temperature	-5...45 °C
Storage/transport temperature	-25...70 °C

Energy-saving	energy saving by means of presence and brightness-dependent ON and OFF switching of light ; low intrinsic energy requirement
---------------	--

**Identification**

Application, usage	Motion detector
Main design line	Motion detectors