



936562507

**Change-over switch, Integro - Design Flow/Pure, grey glossy**

**Technical characteristics**

**Architecture**

|                      |               |
|----------------------|---------------|
| Type of control unit | single rocker |
| Number of keys       | 1             |

**Configuration**

|                         |                 |
|-------------------------|-----------------|
| Switch mode             | Off/change-over |
| Antibacterial treatment | No              |

**Compatibility**

|                         |    |
|-------------------------|----|
| IFTTT support available | No |
|-------------------------|----|

**Main electrical features**

|                 |       |
|-----------------|-------|
| Nominal voltage | 250 V |
|-----------------|-------|

**Electric current**

|                   |   |
|-------------------|---|
| Switching current | 10 AX (100 W Self Ballasted Lamp (SBL)) |
|-------------------|---|

**Dimensions**

|        |         |
|--------|---------|
| Depth  | 25 mm   |
| Height | 55.5 mm |
| Width  | 55.5 mm |

**Materials**

|                    |        |
|--------------------|--------|
| Surface appearance | glossy |
|--------------------|--------|

**Connection**

|                    |                  |
|--------------------|------------------|
| Type of connection | Screw connection |
|--------------------|------------------|

**Equipment**

|                |  |
|----------------|--|
| Lighting       | without lighting (cannot be illuminated) |
| Heating switch | No                                       |

**Use cases**

|             |               |
|-------------|---------------|
| Application | Light control |
|-------------|---------------|

**Safety**

|                     |      |
|---------------------|------|
| Protection index IP | IP44 |
| REACH conform       | Yes  |
| RoHS conform        | Yes  |

**Identification**

|                       |    |
|-----------------------|----|
| Appliance switch type | No |
|-----------------------|----|

